

Alsto LABORATORY BALL & ROD MILLS

The **Alsto** Ball & Rod Mills are designed for simple long term operation. The standard drive unit accepts a variety of different barrel sizes listed below.

- 200 x 200 Ball Mill
- 200 x 250 Rod Mill (pictured)
- 250 x 250 Ball Mill
- 250 x 300 Rod Mill
- 300 x 300 Ball Mill
- 300 x 360 Rod Mill

Noise levels are low due to efficient acoustic enclosure.

This is also fitted with a lock out feature to ensure safe operation.

All moving parts are completely enclosed during operation.

The Alsto Ball & Rod Mills are supplied with a single phase variable speed drive as standard and can be set to suit client requirement.



Features:

- Fully painted mild steel body
- Built in funnel & screen
- MS barrel as standard.
- Stainless steel available on request
- Acoustic enclosure fitted as standard

HS Code 847420 & Associated spares 847490

ALSTO

Phone: +61 (08) 9526 2523 | Email: sales@alsto.com.au
Fax: +61 (08) 9526 2522 | ABN: 41 047 362 761

AUSTRALIAN
TRUSTED
TRADER