

Alsto Filter Press

For de-watering slurried batch samples and concentrates

The **Alsto** Filter Press is ergonomically designed to satisfy most applications.

It is shipped in an ISPM15 compatible crate ready for installation.

The **Alsto** Filter Press has a cylindrical body with filter cloth installed at the bottom. The slurry is poured into the top of the unit. The lid is screwed down securely and manually pressurised using the installed control valve.

The pressurised air then forces the excess moisture from the slurry leaving solids to be concentrated into a cake to be removed at the bottom of the body.

The Filter Presses are available in a variety of material:

- Painted Mild Steel
- 304 Stainless Steel
- 316 Stainless Steel

They are available in a range of sizes:

- 5 & 10L in Bench Mount models
- 13, 21 and 40 litre capacity machines in Floor Mount models



ALSTO

Phone: +61 (08) 9526 2523 | Email: sales@alsto.com.au
Fax: +61 (08) 9526 2522 | ABN: 41 047 362 761

HS Code 847410 & Associated spares 847490